

item Industrietechnik GmbH  
Friedenstraße 107-109  
D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0  
Telefax: +49 / 212 / 65 80 -310  
[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
1*	4	47658	Parallel Fastener 8		
2	2	49301	Profile X 8 80x40 6N light, natural	846 mm	
3*	72	48807	Standard-Fastening Set 8 K		
4	2	61193	Profile X 8 40x40 2N180 light, natural	400 mm	
5	22	48960	Cap X 8 40x40, grey similar to RAL 7042		
6	4	47659	Parallel Fastener 8 Cover Profile, natural	396 mm	
7	4	47660	Parallel Fastener 8 Cover Profile End Cap, black		
8*	1	49216	Acrylic Glass 5mm XT, Clear	868 mm	262 mm
9	4	61190	Profile X 8 40x40 2N90 light, natural	1957 mm	
10	4	49301	Profile X 8 80x40 6N light, natural	45 mm	
11	4	61193	Profile X 8 40x40 2N180 light, natural	1900 mm	
12*	2	49216	Acrylic Glass 5mm XT, Clear	1762 mm	67 mm
13	6	44481	Adapter Plate Profile 80x16 N5, natural	60 mm	
14	4	42766	Profile 8 R40/80-30°, natural	1900 mm	
15	8	42769	Cap 8 R40/80-30°, black		
16	4	49301	Profile X 8 80x40 6N light, natural	876 mm	
17*	2	49216	Acrylic Glass 5mm XT, Clear	1762 mm	898 mm
18	4	49301	Profile X 8 80x40 6N light, natural	560 mm	
19*	2	49216	Acrylic Glass 5mm XT, Clear	1762 mm	582 mm
20	2	61193	Profile X 8 40x40 2N180 light, natural	1957 mm	
21	1	49301	Profile X 8 80x40 6N light, natural	2029 mm	
22	8	48996	Automatic-Fastening Set 8 N		
23	4	48834	Hinge Leaf Profile V 8 z light, natural	40 mm	
24	8	48362	#NV		
25	4	48834	Hinge Leaf Profile V 8 z light, natural	876 mm	
26	2	48834	Hinge Leaf Profile V 8 z light, natural	60 mm	
27*	14	8000517	Countersunk Screw DIN 7991 M6x14, bright zinc-plated		
28*	14	41940	T-Slot Nut 6 St M6, bright zinc-plated		
29	2	61196	Profile X 8 40x40 3N light, natural	1900 mm	
30	4	49301	Profile X 8 80x40 6N light, natural	973 mm	
31*	2	49216	Acrylic Glass 5mm XT, Clear	1762 mm	995 mm
32	4	60161	Angle Bracket Set X 8 80x80		
33	4	49486	Handle X 160 PA, grey similar to RAL 7042		
34	1	49301	Profile X 8 80x40 6N light, natural	860 mm	
35	4	48961	Cap X 8 80x40, grey similar to RAL 7042		
36	2	49288	Profile X 8 40x40 4N light, natural	70 mm	
37*	4	61011	Standard-Fastening Set 8 ESD, bright zinc-plated		
38	2	60162	Angle Bracket Set X 8 40x40		
39*	2	48845	Door Lock 6-8 Zn		
40	2	49301	Profile X 8 80x40 6N light, natural	85 mm	

