

**item Industrietechnik GmbH**  
 Friedenstraße 107-109  
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0  
 Telefax: +49 / 212 / 65 80 -310  
[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
1*	2	2634	Profile 8 80x40 light, natural	1300 mm	
2*	2	2634	Profile 8 80x40 light, natural	520 mm	
3*	2	7000003	Profile 8 40x40 2N180 E, natural	520 mm	
4*	2	7000009	Profile 8 40x40 E, natural	440 mm	
5*	2	36472	Profile 8 80x16, natural	440 mm	
6*	32	2601	Cap 8 40x40, black		
7*	4	46505	Slide Strip 8 antistatic, black	400 mm	
8*	24	42204	Slide Strip Wedge 8, black		
9*	26	26598	Cap 8 80x16, black		
10*	2	7000009	Profile 8 40x40 E, natural	700 mm	
11*	2	36472	Profile 8 80x16, natural	700 mm	
12*	4	46505	Slide Strip 8 antistatic, black	660 mm	
13*	4	7000009	Profile 8 40x40 E, natural	201 mm	
14*	3	7000015	Profile 8 80x16 E, natural	530 mm	
15*	1	2633	Profile 8 40x40 light, natural	690 mm	
16*	2	7000009	Profile 8 40x40 E, natural	690 mm	
17*	2	7000009	Profile 8 40x40 E, natural	273 mm	
18*	1	42846	Plastic 4mm, grey, similar to RAL 7035	632 mm	295 mm
19*	1	49537	Handle X 160 PA, black		
20*	2	48894	Hinge 8 Al PP4, light duty		
21*	1	7000003	Profile 8 40x40 2N180 E, natural	610 mm	
22*	2	42846	Plastic 4mm, grey, similar to RAL 7035	608 mm	238 mm
23*	2	42846	Plastic 4mm, grey, similar to RAL 7035	518 mm	263 mm
24*	6	2602	Cap 8 80x40, black		
25*	2	7000009	Profile 8 40x40 E, natural	260 mm	
26*	4	7000009	Profile 8 40x40 E, natural	550 mm	
27*	4	36472	Profile 8 80x16, natural	550 mm	
28*	8	46505	Slide Strip 8 antistatic, black	510 mm	
29*	4	7000009	Profile 8 40x40 E, natural	430 mm	
30*	4	36472	Profile 8 80x16, natural	430 mm	
31*	8	46505	Slide Strip 8 antistatic, black	390 mm	
32*	4	7000026	Profile 8 80x40 E, natural	43 mm	
33*	4	7000015	Profile 8 80x16 E, natural	135 mm	
34*	8	7000001	Profile 8 40x16 E, natural	113 mm	
35*	16	38808	Automatic-Fastening Set 8, bright zinc-plated		
36*	2	7000009	Profile 8 40x40 E, natural	120 mm	
37*	2	7000006	Profile 8 40x40 2N90 E, natural	279 mm	
38*	2	7000006	Profile 8 40x40 2N90 E, natural	700 mm	
39*	1	7000006	Profile 8 40x40 2N90 E, natural	930 mm	
40*	4	7000003	Profile 8 40x40 2N180 E, natural	660 mm	
41*	1	49497	Profile 8 40x32 light, natural	930 mm	
42*	1	44497	Buffer Strip 8 20x18, black	690 mm	
43*	4	44071	Base Plate/Transport Plate 8 80x40, M10, black		
44*	2	60239	Castor D100 swivel antistatic		
45*	2	60241	Castor D100 swivel with double-brake antistatic		
46*	2	2634	Profile 8 80x40 light, natural	900 mm	
47*	1	41901	Profile 6 30x30, natural	600 mm	
48*	3	44184	Grip Cover Profile 6 30x6, black	600 mm	
49*	1	44184	Grip Cover Profile 6 30x6, black	220 mm	
50*	2	44184	Grip Cover Profile 6 30x6, black	150 mm	

51*	2	44187	Grip End Cap 6 D42, black	
52*	4	41115	Angle Bracket Set 8 40x40	
53*	2	7000009	Profile 8 40x40 E, natural	150 mm
54*	2	2687	Container Mounting 8, black	