

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310
[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
1*	6	7000009	Profile 8 40x40 E, natural	2000 mm	
2*	4	7000009	Profile 8 40x40 E, natural	1255 mm	
3*	2	7000009	Profile 8 40x40 E, natural	2630 mm	
4*	6	26544	L-Based Foot 8 non-adjustable		
5*	2	42846	Plastic 4mm, grey, similar to RAL 7035	1277 mm	1002 mm
6*	4	49209	Acrylic Glass 4mm XT, Clear	1277 mm	1002 mm
7*	3	42767	Profile 8 R40/80-60°, natural	2630 mm	
8*	19	61969	Central-Fastening Set P 8		
9*	8	2601	Cap 8 40x40, black		
10*	6	42770	Cap 8 R40/80-60°, black		
11*	2	44497	Buffer Strip 8 20x18, black	2000 mm	
12*	2	44497	Buffer Strip 8 20x18, black	630 mm	
13*	3	7000009	Profile 8 40x40 E, natural	1350 mm	
14*	2	42846	Plastic 4mm, grey, similar to RAL 7035	1278 mm	1002 mm
15*	1	49209	Acrylic Glass 4mm XT, Clear	1372 mm	932 mm
16*	6	7000009	Profile 8 40x40 E, natural	733 mm	
17*	8	48860	Universal-Fastening Set 8 St, bright zinc-plated		
18*	4	42821	Acrylic Glass 5mm, Clear	1277 mm	756 mm
19*	2	42829	Perforated Sheet Al 3mm, cold rolled (not degreased)	450 mm	1400 mm
20*	2	2633	Profile 8 40x40 light, natural	1264 mm	
21*	2	7000009	Profile 8 40x40 E, natural	1985 mm	
22*	1	7000009	Profile 8 40x40 E, natural	1264 mm	
23*	4	48894	Hinge 8 Al PP4, light duty		
24*	1	48845	Door Lock 6-8 Zn		
25*	1	49209	Acrylic Glass 4mm XT, Clear	1286 mm	1387 mm
26*	1	42846	Plastic 4mm, grey, similar to RAL 7035	1286 mm	522 mm

