

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310
[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
1*	4	118	Profile 12 120x120 light, natural	1560 mm	
2*	32	350	Automatic-Fastening Set 12, bright zinc-plated		
3*	8	118	Profile 12 120x120 light, natural	600 mm	
4*	20	503	Cap 12 120x120, black		
5*	8	776	Castor Adapter Plate 12 M10-105x80		
6*	8	48839	Castor D125 swivel with double-brake, heavy-duty		
10*	12	779	Angle Bracket 12 240x240 Al M12, white aluminium, similar to RAL 9006		
12*	48	60916	Fastening Set for Angle Bracket 12 240x240 M12		
13*	8	368	T-Slot Nut 12 St M12, heavy-duty, bright zinc-plated		
14*	8	41643	Parabolic Buffer M12 D75x89, black		
16*	4	118	Profile 12 120x120 light, natural	800 mm	
17*	8	363	T-Slot Nut 12 St M8, bright zinc-plated		
18*	12	2601	Cap 8 40x40, black		
19*	2	46505	Slide Strip 8 antistatic, black	1800 mm	
20*	4	2633	Profile 8 40x40 light, natural	800 mm	
21*	4	46505	Slide Strip 8 antistatic, black	800 mm	
22*	2	2633	Profile 8 40x40 light, natural	1800 mm	
23*	2	48979	Click-Fastening Set 8		
24*	2	48979	Click-Fastening Set 8		