

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310
 E- Mail: info@item24.com

Item	Quantity	Art. No.	Product description	Length	Width
10	2	62828	Profile Tube D30, natural	1800 mm	
20	6	64096	Threaded Insert D30 M8, grey similar to RAL 7042		
30	6	60244	Knuckle Foot X D40, M8x60, grey similar to RAL 7042		
40	6	62978	Cap, Tube D30, grey similar to RAL 7042		
50	5	62828	Profile Tube D30, natural	1620,00 mm	
60	48	62356	Fastener D30		
70*	24	63039	Anti-Torsion Block 6 D30, grey similar to RAL 7042		
80	2	62828	Profile Tube D30, natural	1090,00 mm	
90	1	62828	Profile Tube D30, natural	1580,00 mm	
100	5	62828	Profile Tube D30, natural	520 mm	
110	2	62828	Profile Tube D30, natural	890 mm	
120	1	62994	Parallel Fastener D30		
130	2	62828	Profile Tube D30, natural	670,00 mm	
140	5	62828	Profile Tube D30, natural	460 mm	
150	4	62828	Profile Tube D30, natural	680 mm	
160	2	62828	Profile Tube D30, natural	935,00 mm	
170	7	63074	Panel Fastener D30		
180	10	63753	Roller Conveyor St D30, grey	886 mm	
190	24	64247	Roller Conveyor St Fastening Bracket D30, bright zinc-plated		
200	10	64707	Roller Conveyor St, Fastening Bracket U D30, bright zinc-plated		
210	10	63753	Roller Conveyor St D30, grey	386 mm	
220	10	64706	Roller Conveyor St, Fastening Bracket I D30, bright zinc-plated		
230	1	63310	Table Top 25-1200x600 plastic coated, grey, similar to RAL 7035		
240	2	63754	Roller Conveyor St D30 with Flanged Wheel, grey	1007 mm	