

item Industrietechnik GmbH
Friedenstraße 107-109
D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
Telefax: +49 / 212 / 65 80 -310
E- Mail: info@item24.com

Item	Quantity	Art. No.	Product description	Length	Width
10	2	62828	Profile Tube D30, natural	932 mm	
20	3	2633	Profile 8 40x40 light, natural	900 mm	
30	15	62856	Tube D30, natural	870 mm	
40	2	62828	Profile Tube D30, natural	516 mm	
50	2	62828	Profile Tube D30, natural	499 mm	
60	2	2633	Profile 8 40x40 light, natural	3000 mm	
70*	4	63753	Roller Conveyor St D30, grey	2929 mm	
80*	4	63753	Roller Conveyor St D30, grey	2884 mm	
90*	4	64179	Roller Conveyor St Guide Rail, grey similar to RAL 7042	2808 mm	
100*	4	64179	Roller Conveyor St Guide Rail, grey similar to RAL 7042	2763 mm	
110*	4	63753	Roller Conveyor St D30, grey	2667 mm	
120*	4	64179	Roller Conveyor St Guide Rail, grey similar to RAL 7042	2547 mm	
130*	4	63753	Roller Conveyor St D30, grey	2462 mm	
140	2	62828	Profile Tube D30, natural	2370 mm	
150*	4	64179	Roller Conveyor St Guide Rail, grey similar to RAL 7042	2340 mm	
160	2	62856	Tube D30, natural	1802 mm	
170	2	62828	Profile Tube D30, natural	1460 mm	
180	2	64234	Profile Tube D30 heavy duty, natural	1449 mm	
190	2	64234	Profile Tube D30 heavy duty, natural	1399 mm	
200*	6	2607	Standard-Fastening Set 8, bright zinc-plated		
210*	50	62356	Fastener D30		
220*	4	62716	Cap 8 40x40, grey similar to RAL 7042		
230*	2	62978	Cap, Tube D30, grey similar to RAL 7042		
240*	4	62994	Parallel Fastener D30		
250*	6	62997	End Connector 8 D30-90°		
260*	2	63051	Adapter 8 D30		
270*	8	63060	Angle Fastener D30		
280*	4	63787	Fastener D30-45°		
290*	6	63913	Castor D100 swivel with double-brake 120x40		
300*	16	64246	Roller Conveyor St, Fastening Bracket D30 with Stop H27, bright zinc-plated		
310*	16	64247	Roller Conveyor St Fastening Bracket D30, bright zinc-plated		
320*	28	64710	Roller Conveyor St, Support D30, bright zinc-plated		