

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310
 E- Mail: info@item24.com

| Item | Quantity | Art. No. | Product description | Length | Width |
|------|----------|----------|--|------------|------------|
| 10 | 6 | 62456 | Profile 10 100x100, natural | 2495 mm | |
| 20 | 6 | 63227 | Cap 10 100x100, grey similar to RAL 7042 | | |
| 30 | 4 | 62456 | Profile 10 100x100, natural | 1400 mm | |
| 40* | 88 | 62508 | Standard-Fastening Set 10, bright zinc-plated | | |
| 50 | 2 | 62460 | Profile 10 100x50, natural | 1400 mm | |
| 60* | 2 | 63238 | Rebate Profile 10 Al M6, natural | 1350 mm | |
| 70 | 1 | 49377 | PET-G 5mm, Clear | 1397,00 mm | 897,00 mm |
| 80* | 14 | 63509 | Multiblock 10 PA, grey | | |
| 90 | 3 | 64194 | Hinge 10 PA 10/8, left, grey similar to RAL 7042 | | |
| 100 | 2 | 2633 | Profile 8 40x40 light, natural | 1296-8 | |
| 110 | 4 | 62716 | Cap 8 40x40, grey similar to RAL 7042 | | |
| 120 | 2 | 2633 | Profile 8 40x40 light, natural | 1317 mm | |
| 130* | 4 | 48807 | Standard-Fastening Set 8 K | | |
| 140* | 1 | 38820 | Ball Latch 8 PA | | |
| 150* | 1 | 49377 | PET-G 5mm, Clear | 1339,00 mm | 1238,00 mm |
| 160 | 2 | 49506 | Double-Lip Seal 8 4-6mm, black | 1317 mm | |
| 170 | 2 | 49506 | Double-Lip Seal 8 4-6mm, black | 1216 mm | |
| 180 | 1 | 49486 | Handle X 160 PA, grey similar to RAL 7042 | | |
| 190 | 12 | 62456 | Profile 10 100x100, natural | 850 mm | |
| 200* | 48 | 2692 | Universal-Fastening Set 8, bright zinc-plated | | |
| 210 | 8 | 63289 | Panel-Clamping Strip 10 Al, natural | 900,00 mm | |
| 220 | 16 | 63289 | Panel-Clamping Strip 10 Al, natural | 818,00 mm | |
| 230 | 8 | 63289 | Panel-Clamping Strip 10 Al, natural | 1300,00 mm | |
| 240* | 16 | 63291 | Panel-Clamping Strip 10 4-6mm, grey similar to RAL 704: 846,00 mm | | |
| 250* | 8 | 63291 | Panel-Clamping Strip 10 4-6mm, grey similar to RAL 704: 888,40 mm | | |
| 260* | 8 | 63291 | Panel-Clamping Strip 10 4-6mm, grey similar to RAL 704: 1283,40 mm | | |
| 270* | 4 | 42843 | Plastic 4mm, red, similar to RAL 3000 | 897,00 mm | 847,00 mm |
| 280* | 4 | 42843 | Plastic 4mm, red, similar to RAL 3000 | 1297,00 mm | 847,00 mm |
| 290* | 4 | 63238 | Rebate Profile 10 Al M6, natural | 800 mm | |
| 300* | 1 | | #NV | | |
| 310 | 1 | 42843 | Plastic 4mm, red, similar to RAL 3000 | 1797,00 mm | 1397,00 mm |
| 320 | 6 | 62520 | Base Plate/Transport Plate 10 100x100, M16, white aluminium, similar to RAL 9006 | | |
| 330 | 6 | 26566 | Knuckle Foot D80, M16x160, black | | |