

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310
[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
10	8	2627	Profile 8 80x80, natural	1040 mm	
20*	64	2607	Standard-Fastening Set 8, bright zinc-plated		
30	4	40623	Base Plate/Transport Plate 8 80x80, M16, black		
40	4	26529	Knuckle Foot D80, M16x100, black		
50	4	45893	Anti-Vibration Insert D80, stainless		
60	4	2627	Profile 8 80x80, natural	2040 mm	
70*	8	41115	Angle Bracket Set 8 40x40		
80*	8	64253	Automatic Flat Bracket Set 8 80x40 Al		
90	2	60502	Linear Unit KLE 8 80x80 LR	1800 mm	
100	2	60924	Carriage Plate KLE 8 80x80		
110*	2	60978	Synchronising Set KLE 8 80x80		
120	1	61245	Synchroniser Shaft Cover Set KLE 8 80x80		
130*	1	46357	Synchronising Shaft Profile VK14, natural	991 mm	
140	1	7000274	Conduit Profile U 80x80 E, natural	1008 mm	
150	1	7000273	Lid Profile D80 E, natural	1008 mm	
160	1	60977	Drive Set KLE 8 80x80		
170	1	2604	Profile 8 80x40, natural	1240 mm	
180	2	44203	Shaft-Clamp Profile 8 D10, natural	1020 mm	
190	2	40109	Shaft D10, bright	1020 mm	
200	4	44209	Bearing Unit 8 D10 e		
210	4	44210	Bearing Unit 8 D10 c		
220	8	44223	End Cap and Lubricating System 8 D10, black		
230	1	26523	Profile 8 160x40, natural	160 mm	
240	2	26539	Cap 8 160x40, black		
250	2	33726	Timing-Belt Reverse Unit 8 40 R25 VK14		
260	1	33710	Timing Belt R25 T10, black	2785 mm	
270	1	2603	Profile 8 40x40, natural	1760 mm	
280*	1	62193	Rack 8 End Section		
290*	21	62194	Rack 8 Segment 80		
300*	1	62169	Rack 8 Drive Module		
310	2	44203	Shaft-Clamp Profile 8 D10, natural	1760 mm	
320	2	40109	Shaft D10, bright	1760 mm	
330	1	41629	Profile 8 120x40, natural	152 mm	
340	2	41854	Cap 8 120x40, black		
350	1	62173	Rack 8 Coupling Module		
360	1	2601	Cap 8 40x40, black		