

**item Industrietechnik GmbH**  
 Friedenstraße 107-109  
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0  
 Telefax: +49 / 212 / 65 80 -310  
[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
10	4	2634	Profile 8 80x40 light, natural	1960 mm	
20	4	2602	Cap 8 80x40, black		
30	4	40632	Base Plate/Transport Plate 8 80x40, M12, black		
40	4	60893	Adjustable Foot 80x40, M12x120		
50*	8	8000911	Button-Head Screw M8x20, bright zinc-plated		
60	6	2634	Profile 8 80x40 light, natural	280 mm	
70*	36	48807	Standard-Fastening Set 8 K		
80*	8	48992	Lip Seal 8 4-6mm, grey, similar to RAL 7040	860 mm	
90*	8	48992	Lip Seal 8 4-6mm, grey, similar to RAL 7040	280 mm	
100	17	2633	Profile 8 40x40 light, natural	1330 mm	
110	35	2692	Universal-Fastening Set 8, bright zinc-plated		
120	8	42892	Plastic 10mm, grey, similar to RAL 7035	360 mm	1327 mm
130*	48	2672	Multiblock 8 PA, black		
140	48		#NV		
150*	4	42846	Plastic 4mm, grey, similar to RAL 7035	880 mm	300 mm
160*	2	2634	Profile 8 80x40 light, natural	1330 mm	
170	1	42846	Plastic 4mm, grey, similar to RAL 7035	342 mm	1330 mm
180	4	48834	Hinge Leaf Profile V 8 z light, natural	40 mm	
190*	14	8000517	Countersunk Screw DIN 7991 M6x14, bright zinc-plated		
200*	22	2623	T-Slot Nut 8 St M6, bright zinc-plated		
210	4	2633	Profile 8 40x40 light, natural	579 mm	
220	4	7000009	Profile 8 40x40 E, natural	1960 mm	
230*	2	42846	Plastic 4mm, grey, similar to RAL 7035	1900 mm	599 mm
240	8	2601	Cap 8 40x40, black		
250	2	2644	Handle, light duty, natural		
260*	4	44442	Locating Washer 8 D5, bright zinc-plated		
270*	4	8000007	Button-Head Screw M5x16, bright zinc-plated		
280	2	48834	Hinge Leaf Profile V 8 z light, natural	1876 mm	
290	4	62116	Hinge Al light, Pin Set D6		
300*	4	37344	T-Slot Nut 8 Zn M5, bright zinc-plated		
310	4	19648	Magnetic Catch 8, black		
320	8	8000092	Hexagon Socket Head Cap Screw DIN 912 M6x20, bright zinc-plated		
330	6	48992	Lip Seal 8 4-6mm, grey, similar to RAL 7040	1330 mm	
340*	2	42846	Plastic 4mm, grey, similar to RAL 7035	920 mm	1350 mm
350*	4	48992	Lip Seal 8 4-6mm, grey, similar to RAL 7040	900 mm	