

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310

E- Mail: info@item24.com

Item	Quantity	Art. No.	Product description	Length	Width
10*	1	48335	Profile 8 200x80, natural	3860 mm	
20*	2	44325	Guide Rail Mounting Profile PS 4-25, natural	2000 mm	
30*	2	44326	Guide Rail Clamping Profile PS 4-25, natural	2000 mm	
40*	2	44325	Guide Rail Mounting Profile PS 4-25, natural	1600 mm	
50*	2	44326	Guide Rail Clamping Profile PS 4-25, natural	1600 mm	
60*	2	44334	Linear Guide Rail PS 4-25	3600 mm	
70*	4	44316	Bearing Carriage PS 4-25		
80*	1	2604	Profile 8 80x40, natural	200 mm	
90*	3	2602	Cap 8 80x40, black		
100*	1	47382	Profile 8 200x40, natural	139 mm	
110*	1	47382	Profile 8 200x40, natural	119 mm	
120*	4	43623	Angle Bracket 8 160x80 Zn, white aluminium, similar to RAL 9006		
130*	5	2607	Standard-Fastening Set 8, bright zinc-plated		
140*	2	47401	Cap 8 200x40, black		
150*	2	42621	Timing-Belt Reverse Unit 8 80 R50 II with Bore		
160*	1	42603	Timing Belt R50 T10, black	8312 mm	
170*	2	42604	Timing-Belt Tensioner, Tensioning Block 8 R50		
180*	1	42605	Timing-Belt Tensioner, Fixing Block 8 R50		
190*	2	8000470	Hexagon Socket Head Cap Screw DIN 912 M6x100, bright zinc-plated		
200*	2	2637	Cap 8 80x80, black		
210*	1	2601	Cap 8 40x40, black		
220*	1	41433	Ball Screw Unit KGT 20x5, VK14	738 mm	
230*	2	29434	Shaft-Clamp Profile 8 D14, natural	738 mm	
240*	2	29401	Shaft D14, bright	738 mm	
250*	2	29414	Bearing Unit 8 D14 c		
260*	2	29415	Bearing Unit 8 D14 e		
270*	4	29446	End Cap and Lubricating System 8 D14, black		
280*	1	47386	Profile 8 200x28, natural	360 mm	
290*	2	47407	Cap 8 200x28, black		