

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310
[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
10	4	65181	Cap X 8 120x120-45° Al		
30	8	65063	Cap Set, Door Profile X 8 40x40 - XMS		
40	8	65063	Cap Set, Door Profile X 8 40x40 - XMS		
50*	2	64783	Cover Profile 15 K, grey similar to RAL 7042	680 mm	
60*	4	64783	Cover Profile 15 K, grey similar to RAL 7042	700 mm	
70	4	64782	Cover Profile 56 K, grey similar to RAL 7042	1500 mm	
80*	4	64782	Cover Profile 56 K, grey similar to RAL 7042	920 mm	
90	208	38808	Automatic-Fastening Set 8, bright zinc-plated		
100*	2	65181	Cap X 8 120x120-45° Al	880 mm	80 mm
110*	2	65181	Cap X 8 120x120-45° Al	116 mm	
120*	1	65181	Cap X 8 120x120-45° Al	800 mm	
130*	1	65181	Cap X 8 120x120-45° Al	840 mm	
140*	4	64993	Lip Seal 4-5 mm - XMS, grey	2312 mm	
150*	12	64993	Lip Seal 4-5 mm - XMS, grey	812 mm	
160*	4	64993	Lip Seal 4-5 mm - XMS, grey	712 mm	
170*	4	64993	Lip Seal 4-5 mm - XMS, grey	940 mm	
190*	6	60651	Rubber Insert X D80, black		
200*	8	64383	Conduit Corner Cap 8 40 - XMS, grey similar to RAL 7042		
210*	4	63351	Conduit Cap 80x40 K, grey similar to RAL 7042		
220*	1	64805	Conduit Profile U 80x80 K, grey similar to RAL 7042	803 mm	
230*	1	64805	Conduit Profile U 80x80 K, grey similar to RAL 7042	760 mm	
240*	2	64805	Conduit Profile U 80x80 K, grey similar to RAL 7042	680 mm	
250*	2	64805	Conduit Profile U 80x80 K, grey similar to RAL 7042	116 mm	
260	4	49596	Foot Clamp X D80, white aluminium, similar to RAL 9006		
270*	28	64385	Clip 8, Conduit Profile K, grey similar to RAL 7042		
280*	1		#NV	2120 mm	1040 mm
290*	24	2618	T-Slot Nut 8 St M8, bright zinc-plated		
300*	2	48350	Polycarbonate 4mm, Clear	1020 mm	832 mm
310*	2	48350	Polycarbonate 4mm, Clear	940 mm	732 mm
340*	2	42823	Polycarbonate 5mm, Clear	873 mm	933 mm
350	4	64303	Profile X 8 120x120 K56 - XMS, natural	2500 mm	
360*	2	61187	Profile X 8 40x40 1N light, natural	900 mm	
370	6	64938	Profile X 8 80x40 1N - XMS, natural	900 mm	
380	4	64938	Profile X 8 80x40 1N - XMS, natural	800 mm	
400*	2	64307	Profile X 8 80x40 2N K15 - XMS, natural	900 mm	
410	2	49294	Profile X 8 80x40 light, natural	880 mm	
420	2	64305	Profile X 8 80x80 2N K15 - XMS, natural	800 mm	
430*	2	64305	Profile X 8 80x80 2N K15 - XMS, natural	900 mm	
450	4	64939	Profile X 8 80x80 2N - XMS, natural	900 mm	
460	2	64939	Profile X 8 80x80 2N - XMS, natural	2500 mm	
480	2	64939	Profile X 8 80x80 2N - XMS, natural	800 mm	
500*	2	49297	Profile X 8 80x80 light, natural	880 mm	
510	16	62116	Hinge Al light, Pin Set D6		
520	10	48834	Hinge Leaf Profile V 8 z light, natural	40 mm	
530	2	48834	Hinge Leaf Profile V 8 z light, natural	40 mm	
540	2	48834	Hinge Leaf Profile V 8 z light, natural	40 mm	
550	2	48834	Hinge Leaf Profile V 8 z light, natural	40 mm	
560	2	48834	Hinge Leaf Profile V 8 z light, natural	80 mm	
570	2	48834	Hinge Leaf Profile V 8 z light, natural	40 mm	
580*	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	840 mm	

590*	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	788 mm	
600*	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	880 mm	
610*	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	928 mm	
630*	4	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	1000 mm	
640*	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	420 mm	
650*	12	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	888 mm	
660*	4	49505	Panel-Clamping Strip 8 Al, natural	1000 mm	
670	8	49505	Panel-Clamping Strip 8 Al, natural	908 mm	
690	8	49505	Panel-Clamping Strip 8 Al, natural	880 mm	
700	8	49505	Panel-Clamping Strip 8 Al, natural	768 mm	
710	8	49505	Panel-Clamping Strip 8 Al, natural	840 mm	
720	8	49505	Panel-Clamping Strip 8 Al, natural	420 mm	
730*	12	49505	Panel-Clamping Strip 8 Al, natural	868 mm	
740*	16	65061	Clamping Set, Door Profile X 8 - XMS		
750	6	49603	Knuckle Foot X D80, M16x100, white aluminium, similar to RAL 9006		
760	4	65062	Base Plate/Transport Plate X 8 200x200-90° M16		
770	2	65263	Base Plate/Transport Plate X 8 240x160-2x90° M16		
780*	4	-64989	#NV	2000 mm	
790*	4	-64989	#NV	380 mm	
800*	4	-64989	#NV	900 mm	
810*	2	-64989	#NV	880 mm	
820*	4	-64989	#NV	1000 mm	
830*	2	-64989	#NV	800 mm	
840	2	65240	Door Profile X 8 80x40-180° - XMS, natural	812 mm	
860	4	649501	#NV	984 mm	
870	4	649501	#NV	2356 mm	
880	4	649501	#NV	712 mm	
890	4	649501	#NV	812 mm	
900	2	64956	#NV	812 mm	
920*	14	64809	Catch 80, Conduit Profile K, grey similar to RAL 7042		
930*	2	47437	Plastic 4mm, black, similar to RAL 9017	396 mm	832 mm
940*	2	47437	Plastic 4mm, black, similar to RAL 9017	413 mm	893 mm
950*	2	47437	Plastic 4mm, black, similar to RAL 9017	833 mm	793 mm
970*	2	47437	Plastic 4mm, black, similar to RAL 9017	816 mm	832 mm
990*	2	47437	Plastic 4mm, black, similar to RAL 9017	993 mm	893 mm
1010*	2	47437	Plastic 4mm, black, similar to RAL 9017	833 mm	893 mm
1020*	2	47437	Plastic 4mm, black, similar to RAL 9017	413 mm	793 mm
1030	2	47437	Plastic 4mm, black, similar to RAL 9017	873 mm	933 mm
1040*	16	8000434	Hexagon Socket Head Cap Screw DIN 6912 M5x8, bright zinc-plated		
1050*	24	8000434	Hexagon Socket Head Cap Screw DIN 6912 M5x8, bright zinc-plated		
1060*	28	8000636	Hexagon Socket Head Cap Screw DIN 912 M8x60, bright zinc-plated		
1070*	2	65139	Cap X 8 80x80 Al		
1080*	4	65266	Door Lock X 8 Zn		
1090*	4	65266	Door Lock X 8 Zn		