

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310
[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
10	4	45759	Profile 8 80x80 4N90 light, natural	2500 mm	
20	6	62720	Cap 8 80x80, grey similar to RAL 7042		
30	6	40623	Base Plate/Transport Plate 8 80x80, M16, black		
40	6	26529	Knuckle Foot D80, M16x100, black		
50	4	26530	Foot Clamp D80, black		
60	6	60775	Profile 8 80x40 1N light, natural	940 mm	
70	208	38808	Automatic-Fastening Set 8, bright zinc-plated		
80	2	45752	Profile 8 80x80 2N light, natural	2500 mm	
90	6	45752	Profile 8 80x80 2N light, natural	940 mm	
100*	2	42272	Profile 8 40x40 1N light, natural	940 mm	
110*	2	42275	Profile 8 80x40 2N light, natural	940 mm	
120	4	60775	Profile 8 80x40 1N light, natural	880 mm	
130	4	45752	Profile 8 80x80 2N light, natural	880 mm	
140	2	2634	Profile 8 80x40 light, natural	880 mm	
150*	2	26580	Profile 8 80x80 light, natural	880 mm	
160	8	49505	Panel-Clamping Strip 8 Al, natural	100 mm	
170	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	100 mm	
180	20	49505	Panel-Clamping Strip 8 Al, natural	908 mm	
190*	20	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	908 mm	
200	8	49505	Panel-Clamping Strip 8 Al, natural	100,00 mm	
210*	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	100,00 mm	
220*	4	49505	Panel-Clamping Strip 8 Al, natural	100 mm	
230*	4	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	100 mm	
240	8	49505	Panel-Clamping Strip 8 Al, natural	840 mm	
250*	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	840 mm	
260	8	49505	Panel-Clamping Strip 8 Al, natural	848,00 mm	
270*	8	49503	Panel-Clamping Strip 8 4-6mm, grey similar to RAL 7042	848,00 mm	
280*	2	42823	Polycarbonate 5mm, Clear	880 mm	940 mm
290	2	47437	Plastic 4mm, black, similar to RAL 9017	940 mm	880 mm
300*	2	47437	Plastic 4mm, black, similar to RAL 9017	420 mm	940 mm
310*	2	47437	Plastic 4mm, black, similar to RAL 9017	1000 mm	940 mm
320*	2	47437	Plastic 4mm, black, similar to RAL 9017	840 mm	940 mm
330	2	47437	Plastic 4mm, black, similar to RAL 9017	420 mm	880 mm
340	2	47437	Plastic 4mm, black, similar to RAL 9017	840 mm	880 mm
350	2	61732	Door Stop Seal 8 40, grey similar to RAL 7042	2380 mm	
360	4	19650	Clamp Profile 8 40x40, natural	2364 mm	
370	4	19650	Clamp Profile 8 40x40, natural	852 mm	
380	4	65266	Door Lock X 8 Zn		
390	16	62716	Cap 8 40x40, grey similar to RAL 7042		
400	12	48834	Hinge Leaf Profile V 8 z light, natural	80 mm	
410	16	62116	Hinge Al light, Pin Set D6		
420	6	48834	Hinge Leaf Profile V 8 z light, natural	677 mm	
430	4	48336	Clamp Profile 8 40x40-180° light, natural	852 mm	
440*	24	8000010	Button-Head Screw M8x40, bright zinc-plated		
450*	2	47437	Plastic 4mm, black, similar to RAL 9017	416 mm	892 mm
460*	2	47437	Plastic 4mm, black, similar to RAL 9017	876 mm	892 mm
470*	2	48350	Polycarbonate 4mm, Clear	1040 mm	892 mm
480	4	19650	Clamp Profile 8 40x40, natural	984 mm	
490	4	19650	Clamp Profile 8 40x40, natural	792 mm	
500	2	48834	Hinge Leaf Profile V 8 z light, natural	820 mm	

510*	2	48350	Polycarbonate 4mm, Clear	952 mm	832 mm
520*	2	61732	Door Stop Seal 8 40, grey similar to RAL 7042	1000 mm	
530*	1		#NV		
540*	1	19637	Support Profile 40 with groove 8, natural	2300 mm	
550*	2	19639	Wall Profile 40, natural	2300 mm	
560*	1	19638	Support Profile 40, natural	2300 mm	
570*	12	7000118	Profile M 40x4 E, natural	80 mm	
580*	2	19637	Support Profile 40 with groove 8, natural	1900 mm	
590*	4	19639	Wall Profile 40, natural	1900 mm	
600*	2	19638	Support Profile 40, natural	1900 mm	