

Item	Quantity	Art. No.	Product description	Length	Width
10*	10	2633	Profile 8 40x40 light, natural	1180 mm	
20*	10	2633	Profile 8 40x40 light, natural	670+275	
30*	20	62716	Cap 8 40x40, grey similar to RAL 7042		
40*	40	38808	Automatic-Fastening Set 8, bright zinc-plated		
50*	20	63348	Castor D125 swivel with double-brake 120x40		
60*	20	62997	End Connector 8 D30-90°		
70*	20	62828	Profile Tube D30, natural	1450 mm	
80*	95	62978	Cap, Tube D30, grey similar to RAL 7042		
90*	10	62828	Profile Tube D30, natural	835 mm	
100*	90	62356	Fastener D30		
110*	10	62828	Profile Tube D30, natural	250 mm	
120*	20	63787	Fastener D30-45°		
130*	10	62856	Tube D30, natural	310 mm	
140*	50	62828	Profile Tube D30, natural	1260 mm	
150*	50	64246	Roller Conveyor St, Fastening Bracket D30 with Stop H27, bright zinc-plated		
160*	50	64247	Roller Conveyor St Fastening Bracket D30, bright zinc-plated		
170*	90	63790	Transverse Fastener D30		
180*	10	62828	Profile Tube D30, natural	300 mm	
190*	10	62828	Profile Tube D30, natural	1150 mm	
200*	10	62995	Bracing Strut D30-90°		
210*	5	64797	Light Fitting 36W, 230V		
220*	20	63051	Adapter 8 D30		
230*	110	62994	Parallel Fastener D30		
240*	10	62828	Profile Tube D30, natural	1200 mm	
250*	100	62691	Castor Rail 8 40x40, natural	900 mm	
260*	600	62709	Castor Insert D30 with Flanged Wheel, signal red similar to RAL 3001		
270*	600	62710	Castor Insert D30 with Flanged Wheel, signal yellow similar to RAL 1003		
280*	600	62711	Castor Insert D30 with Flanged Wheel, signal green similar to RAL 6032		
290*	108	62229	Castor Rail 8 Cap 40x40		
300*	100	62230	Castor Rail 8 Cap 80x40		
310*	20	64691	Table-Top Fastening Set D30		
320*	10	62856	Tube D30, natural	1475 mm	
330*	4	62691	Castor Rail 8 40x40, natural	4500 mm	
340*	7	62220	Railing Support 8/5 100x80		
350*	4	39106	Profile 5 40x10, natural	3000 mm	
360*	18	39114	Cap 5 40x10, black		
370*	14	7000001	Profile 8 40x16 E, natural	239 mm	
380*	24	2633	Profile 8 40x40 light, natural	243 mm	
390*	7	42892	Plastic 10mm, grey, similar to RAL 7035	390 mm	316 mm
400*	28	64054	Bracket 8 120x40 flat, black		
410*	8	47436	Plastic 10mm, black, similar to RAL 9017	400 mm	300 mm
420*	2	39106	Profile 5 40x10, natural	1676 mm	
430*	1	39106	Profile 5 40x10, natural	1488 mm	
440*	16	62226	Castor Rail 8 40x40, Slide Strip ESD, black	100 mm	
450*	104	62006	Castor Insert D30 with Flanged Wheel, black similar to RAL 9005		
460*	16	62026	Castor Ball Insert ESD		
470*	48	62226	Castor Rail 8 40x40, Slide Strip ESD, black	106 mm	
480*	12	62226	Castor Rail 8 40x40, Slide Strip ESD, black	102 mm	
490*	4	62084	Slide Strip Wedge Insert ESD		
500*	10	2633	Profile 8 40x40 light, natural	380-137	

510*	52	2607	Standard-Fastening Set 8, bright zinc-plated		
520*	22	19687	Angle Bracket 8 40 right-angled, black		
530*	24	42016	Castor D75 swivel with double-brake		
540*	40	41132	Angle Bracket Set 8 80x80		
550*	20	2633	Profile 8 40x40 light, natural	743 mm	
560*	1	39106	Profile 5 40x10, natural	1500 mm	
570*	2	63331	Table Top 40-1200x600 Beech multi-ply, UV lacquer	420 mm	420 mm
580*	8	62220	Railing Support 8/5 100x80		
590*	2	39106	Profile 5 40x10, natural	348 mm	
600*	2	39106	Profile 5 40x10, natural	116 mm	
610*	24	62093	Castor Ball Set, bright zinc-plated		
620*	2	62691	Castor Rail 8 40x40, natural	1626 mm	
630*	1	39106	Profile 5 40x10, natural	1976 mm	
640*	12	62226	Castor Rail 8 40x40, Slide Strip ESD, black	139 mm	
650*	4	2633	Profile 8 40x40 light, natural	763 mm	
660*	4	2633	Profile 8 40x40 light, natural	120 mm	
670*	4	2633	Profile 8 40x40 light, natural	320 mm	
680*	1	43336		#NV	400 mm 200 mm
690*	2	39106	Profile 5 40x10, natural	600 mm	
700*	2	2633	Profile 8 40x40 light, natural	302 mm	
710*	4	26531	Hinge 8 40x40, heavy-duty		
720*	1	2633	Profile 8 40x40 light, natural	435 mm	
730*	1	2633	Profile 8 40x40 light, natural	234 mm	
740*	2	39102	Profile 5 20x10, natural	200 mm	
750*	20	63060	Angle Fastener D30		