

item Industrietechnik GmbH  
Friedenstraße 107-109  
D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0  
Telefax: +49 / 212 / 65 80 -310  
E- Mail: [info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
10	2	41666	Profile 8 120x40 light, natural	2000 mm	
20	2	65089	Frame Profile 8 120x40 light, natural	1910 mm	
30	1	65014	Step Profile 8 160, natural	1959 mm	
40	7	65015	Step Profile 8 240, natural	1959 mm	
50*	7	65174	Platform Cleat		
60*	1	2634	Profile 8 80x40 light, natural	1910 mm	
70*	12	2607	Standard-Fastening Set 8, bright zinc-plated		
80*	7	65174	Platform Cleat		
90*	4	65529	Glide Tape 15x0.15 SA	1910 mm	
100*	8	65309	Angle Bracket 8 40x40x40 St		
110	4	62727	Cap 8 120x40, grey similar to RAL 7042		
120	1	65312	Stairway Assembly Set GP 45°		
130	2	41666	Profile 8 120x40 light, natural	3390 mm	
140	12	64715	Step Profile Bracket Set 8 240		
150	12	65015	Step Profile 8 240, natural	990 mm	
160	7	62023	Hand-Rail Joint		
170	10	49342	Profile 8 D40 2N180, natural	1136 mm	
180	18	65144	Stanchion Base Socket		
190	10	62022	Stanchion Fastener		
200	26	62028	Knee-Rail Angle Fastener		
210	1	49345	Profile 8 D40 3N, natural	2030 mm	
220	2	61649	Profile 6 D30 4N, natural	810 mm	
230	1	65086	Profile 8 120x16 E, natural	1960 mm	
240	9	65087	Cap 8 120x16, grey similar to RAL 7042		
250*	1	42223	Cover Profile 8, natural	2030 mm	
260	2	49345	Profile 8 D40 3N, natural	2020 mm	
270	2	61649	Profile 6 D30 4N, natural	805 mm	
280	1	65086	Profile 8 120x16 E, natural	1950 mm	
290*	2	42223	Cover Profile 8, natural	2020 mm	
300	2	61649	Profile 6 D30 4N, natural	890 mm	
310	1	65086	Profile 8 120x16 E, natural	2090 mm	
320	2	49342	Profile 8 D40 2N180, natural	1059 mm	
330	6	62024	Stanchion Angle Fastener		
340	4	49342	Profile 8 D40 2N180, natural	1004 mm	
350	6	61649	Profile 6 D30 4N, natural	988 mm	
360	2	49342	Profile 8 D40 2N180, natural	1055 mm	
370	2	49345	Profile 8 D40 3N, natural	3457 mm	
380*	2	42223	Cover Profile 8, natural	3537 mm	
390	1	49345	Profile 8 D40 3N, natural	870 mm	
400	1	61649	Profile 6 D30 4N, natural	580 mm	
410	1	65086	Profile 8 120x16 E, natural	900 mm	
420	1	65086	Profile 8 120x16 E, natural	132 mm	
430*	1	42223	Cover Profile 8, natural	870 mm	
440*	2	38808	Automatic-Fastening Set 8, bright zinc-plated		
450	4	26566	Knuckle Foot D80, M16x160, black		
460	4	40633	Base Plate/Transport Plate 8 80x40, M16, black		
470	4	2634	Profile 8 80x40 light, natural	2414 mm	
480	8	61956	Angle Bracket 8 160x160-40 Al M8, white aluminium, similar to RAL 9006		
490*	16	47996	Fastening Set for Angle Bracket 8 160x160 M8		