

item Industrietechnik GmbH
 Friedenstraße 107-109
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0
 Telefax: +49 / 212 / 65 80 -310

[E- Mail: info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
10	2	65312	Stairway Assembly Set GP 45°		
20	4	41666	Profile 8 120x40 light, natural	873 mm	
30	8	64715	Step Profile Bracket Set 8 240		
40	8	65015	Step Profile 8 240, natural	830 mm	
50	4	49342	Profile 8 D40 2N180, natural	1059 mm	
60	14	65144	Stanchion Base Socket		
70	4	62024	Stanchion Angle Fastener		
80	24	62028	Knee-Rail Angle Fastener		
90	8	62023	Hand-Rail Joint		
100	4	61649	Profile 6 D30 4N, natural	752 mm	
110	4	49342	Profile 8 D40 2N180, natural	1055 mm	
120	4	49345	Profile 8 D40 3N, natural	940 mm	
130*	4	42223	Cover Profile 8, natural	1020 mm	
140	2	41666	Profile 8 120x40 light, natural	920 mm	
150	2	65089	Frame Profile 8 120x40 light, natural	3830 mm	
160	2	65014	Step Profile 8 160, natural	879 mm	
170	14	65015	Step Profile 8 240, natural	879 mm	
180*	15	65174	Platform Cleat		
190*	6	65309	Angle Bracket 8 40x40x40 St		
200	4	62727	Cap 8 120x40, grey similar to RAL 7042		
210*	8	2607	Standard-Fastening Set 8, bright zinc-plated		
220*	2	65529	Glide Tape 15x0.15 SA	3830 mm	
230	2	49345	Profile 8 D40 3N, natural	3940 mm	
240	6	62022	Stanchion Fastener		
250	6	49342	Profile 8 D40 2N180, natural	1136 mm	
260	8	61649	Profile 6 D30 4N, natural	908 mm	
270	2	65086	Profile 8 120x16 E, natural	4150 mm	
280	4	65087	Cap 8 120x16, grey similar to RAL 7042		
290*	2	42223	Cover Profile 8, natural	3940 mm	
300	6	44071	Base Plate/Transport Plate 8 80x40, M10, black		
310	6	43930	Knuckle Foot D60, M10x120, black		
320	6	2634	Profile 8 80x40 light, natural	634 mm	
330	12	61956	Angle Bracket 8 160x160-40 Al M8, white aluminium, similar to RAL 9006		
340*	24	47996	Fastening Set for Angle Bracket 8 160x160 M8		