

item Industrietechnik GmbH  
 Friedenstraße 107-109  
 D- 42699 Solingen



Telefon: +49 / 212 / 65 80 -0  
 Telefax: +49 / 212 / 65 80 -310  
 E- Mail: [info@item24.com](mailto:info@item24.com)

Item	Quantity	Art. No.	Product description	Length	Width
10	10	46579	Bed Plate Profile 8 152x20, natural	1000 mm	
20	9	46580	Bed Plate Connection Profile 8 55x20, natural	1000 mm	
30	2	2634	Profile 8 80x40 light, natural	840 mm	
40	3	2634	Profile 8 80x40 light, natural	1880 mm	
50*	13	8000019	Button-Head Screw M8x16, bright zinc-plated	16 mm	
60*	13	41611	Washer 13.5x9x1, bright zinc-plated		
70*	15	2618	T-Slot Nut 8 St M8, bright zinc-plated		
80*	22	2607	Standard-Fastening Set 8, bright zinc-plated		
90	8	64254	Automatic Angle Bracket Set 8 40x40 Al		
100	4	2634	Profile 8 80x40 light, natural	834 mm	
110	4	40632	Base Plate/Transport Plate 8 80x40, M12, black		
120	4	60893	Adjustable Foot 80x40, M12x120		
130	3	2634	Profile 8 80x40 light, natural	1000 mm	
140*	1	64595	Tray 6x4 ESD A		
150	2	2633	Profile 8 40x40 light, natural	1146 mm	
160	22	38808	Automatic-Fastening Set 8, bright zinc-plated		
170	2	2633	Profile 8 40x40 light, natural	654 mm	
180	3	62718	Cap 8 80x40, grey similar to RAL 7042		
190	1	2633	Profile 8 40x40 light, natural	1880 mm	
200	2	2633	Profile 8 40x40 light, natural	840 mm	
210	1	60319	Drawer Unit S3 H383, grey similar to RAL 7042		
220	1	61100	Ball Joint 8, Socket with Clamp Lever		
230	2	61095	Ball Joint 8, Ball End 40x40		
240	1	2633	Profile 8 40x40 light, natural	800 mm	
250	1	45778	Angle Clamp Bracket 8 with Clamp Lever		
260	1	45776	Angle Hinge Bracket 8		
270	1	41760	Lamp 35W		
280	2	2633	Profile 8 40x40 light, natural	400 mm	
290	1	47444	Face Fastening Set 8, black		
300	2	2633	Profile 8 40x40 light, natural	600 mm	
310	7	62716	Cap 8 40x40, grey similar to RAL 7042		
320*	2	8000268	Button-Head Screw M8x50, bright zinc-plated		
330	1		#NV		
340	1	47444	Face Fastening Set 8, black		
350	2	41637	Impact Buffer M8 D30x30, black		